



3-Point Mask for Other Systems



RT-1782ORF3	Aquaplast RT 3-Point Mask, 2.4 mm, 40% perforated
RT-1778ORF3	Aquaplast RT 3-Point Mask, 2.4 mm, 20% perforated
RT-1782KORF3	Fibreplast 3-Point Mask, 2.4 mm, 40% perforated
RT-1778KORF3	Fibreplast 3-Point Mask, 2.4 mm, 20% perforated

4-Point Mask for Other Systems




RT-1782ORF4	Aquaplast RT 4-Point Mask, 2.4 mm, 40% perforated
RT-1778ORF4	Aquaplast RT 4-Point Mask, 2.4 mm, 20% perforated
RT-1782KORF4	Fibreplast 4-Point Mask, 2.4 mm, 40% perforated
RT-1778KORF4	Fibreplast 4-Point Mask, 2.4 mm, 20% perforated

5-Point Mask for Other Systems




RT-1782ORF5	Aquaplast RT 5-Point Mask, 2.4 mm, 40% perforated
RT-1778ORF5	Aquaplast RT 5-Point Mask, 2.4 mm, 20% perforated
RT-1782KORF5	Fibreplast 5-Point Mask, 2.4 mm, 40% perforated
RT-1778KORF5	Fibreplast 5-Point Mask, 2.4 mm, 20% perforated

2-Point Mask for Other Systems




RT-1782PR2	Aquaplast RT 2-Point Mask, 2.4 mm, 40% perforated
RT-1778PR2	Aquaplast RT 2-Point Mask, 2.4 mm, 20% perforated
RT-1782KPR2	Fibreplast 2-Point Mask, 2.4 mm, 40% perforated
RT-1778KPR2	Fibreplast 2-Point Mask, 2.4 mm, 20% perforated

3-Point Mask for Other Systems




RT-1782PR3	Aquaplast RT 3-Point Mask, 2.4 mm, 40% perforated
RT-1778PR3	Aquaplast RT 3-Point Mask, 2.4 mm, 20% perforated
RT-1782KPR3	Fibreplast 3-Point Mask, 2.4 mm, 40% perforated
RT-1778KPR3	Fibreplast 3-Point Mask, 2.4 mm, 20% perforated

4-Point Mask for Other Systems




RT-1782PR4	Aquaplast RT 4-Point Mask, 2.4 mm, 40% perforated
RT-1778PR4	Aquaplast RT 4-Point Mask, 2.4 mm, 20% perforated
RT-1782KPR4	Fibreplast 4-Point Mask, 2.4 mm, 40% perforated
RT-1778KPR4	Fibreplast 4-Point Mask, 2.4 mm, 20% perforated

5-Point Mask for Other Systems




RT-1782PR5	Aquaplast RT 5-Point Mask, 2.4 mm, 40% perforated
RT-1778PR5	Aquaplast RT 5-Point Mask, 2.4 mm, 20% perforated
RT-1782KPR5	Fibreplast 5-Point Mask, 2.4 mm, 40% perforated
RT-1778KPR5	Fibreplast 5-Point Mask, 2.4 mm, 20% perforated



2-Point Mask for Other Systems

RT-1782PR2D	Aquaplast RT 2-Point Mask with disposable lockers 2.4 mm, 40% perforated
RT-1778PR2D	Aquaplast RT 2-Point Mask with disposable lockers 2.4 mm, 20% perforated
RT-1782KPR2D	Fibreplast 2-Point Mask with disposable lockers 2.4 mm, 40% perforated
RT-1778KPR2D	Fibreplast 2-Point Mask with disposable lockers 2.4 mm, 20% perforated



3-Point Mask for Other Systems

RT-1782PR3D	Aquaplast RT 3-Point Mask with disposable lockers 2.4 mm, 40% perforated
RT-1778PR3D	Aquaplast RT 3-Point Mask with disposable lockers 2.4 mm, 20% perforated
RT-1782KPR3D	Fibreplast 3-Point Mask with disposable lockers 2.4 mm, 40% perforated
RT-1778KPR3D	Fibreplast 3-Point Mask with disposable lockers 2.4 mm, 20% perforated



4-Point Mask for Other Systems

RT-1782PR4D	Aquaplast RT 4-Point Mask with disposable lockers 2.4 mm, 40% perforated
RT-1778PR4D	Aquaplast RT 4-Point Mask with disposable lockers 2.4 mm, 20% perforated
RT-1782KPR4D	Fibreplast 4-Point Mask with disposable lockers 2.4 mm, 40% perforated
RT-1778KPR4D	Fibreplast 4-Point Mask with disposable lockers 2.4 mm, 20% perforated




5-Point Mask for Other Systems

RT-1782PR5D	Aquaplast RT 5-Point Mask with disposable lockers 2.4 mm, 40% perforated
RT-1778PR5D	Aquaplast RT 5-Point Mask with disposable lockers 2.4 mm, 20% perforated
RT-1782KPR5D	Fibreplast 5-Point Mask with disposable lockers 2.4 mm, 40% perforated
RT-1778KPR5D	Fibreplast 5-Point Mask with disposable lockers 2.4 mm, 20% perforated

Aquaplast RT™ / Fibreplast™ for Portrait™ Head & Neck Device & Other Systems




Head & Neck Patient set up for treatment on a Portrait™ Head & Neck Device with a Fibreplast Head-Only S-Frame




Head-Only S-Frame for Portrait™ & Other Systems - Standard

RT-1679SD	Aquaplast RT Head-Only Portrait S-Frame, 1.6 mm, Standard
RT-1779SD	Aquaplast RT Head-Only Portrait S-Frame, 2.4 mm, Standard
RT-1779KSD	Fibreplast Head-Only Portrait S-Frame, 2.4 mm, Standard
RT-1889SD	Aquaplast RT Head-Only Portrait S-Frame, 3.2 mm, Standard
RT-1889KSD	Fibreplast Head-Only Portrait S-Frame, 3.2 mm, Standard




Head-Only S-Frame for Portrait™ & Other Systems - Extended

RT-1679SDX	Aquaplast RT Head-Only Portrait S-Frame, 1.6 mm, Extended
RT-1779SDX	Aquaplast RT Head-Only Portrait S-Frame, 2.4 mm, Extended
RT-1779KSDX	Fibreplast Head-Only Portrait S-Frame, 2.4 mm, Extended
RT-1889SDX	Aquaplast RT Head-Only Portrait S-Frame, 3.2 mm, Extended
RT-1889KSDX	Fibreplast Head-Only Portrait S-Frame, 3.2 mm, Extended




Head-Only S-Frame for Portrait™ & Other Systems - Long

RT-1679SDL	Aquaplast RT Head-Only Portrait S-Frame, 1.6 mm, Long
RT-1779SDL	Aquaplast RT Head-Only Portrait S-Frame, 2.4 mm, Long
RT-1779KSDL	Fibreplast Head-Only Portrait S-Frame, 2.4 mm, Long
RT-1889SDL	Aquaplast RT Head-Only Portrait S-Frame, 3.2 mm, Long
RT-1889KSDL	Fibreplast Head-Only Portrait S-Frame, 3.2 mm, Long



Split-Frame- Head Only S-Frame with 8 cm Gap for Portrait™ & CURVE™

RT-1779SD-S3	Aquaplast RT Disposable Head-Only Split-Frame S-Frame, 2.4 mm, perforated
RT-1889SD-S3	Aquaplast RT Disposable Head-Only Split-Frame S-Frame, 3.2 mm, perforated
RT-1779KSD-S3	Fibreplast with Kevlar® Disposable Head-Only Split-Frame S-Frame, 2.4 mm, perforated
RT-1889KSD-S3	Fibreplast with Kevlar® Disposable Head-Only Split-Frame S-Frame, 3.2 mm, perforated



Head & Shoulder S-Frame Mask for Portrait™ & Other Systems

RT-1682SD	Aquaplast RT Head & Shoulder Portrait S-Frame, 1.6 mm
RT-1782SD	Aquaplast RT Head & Shoulder Portrait S-Frame, 2.4 mm
RT-1782KSD	Fibreplast Head & Shoulder Portrait S-Frame, 2.4 mm
RT-1892SD	Aquaplast RT Head & Shoulder Portrait S-Frame, 3.2 mm
RT-1892KSD	Fibreplast Head & Shoulder Portrait S-Frame, 3.2 mm



Variable Perf Head-Only Portrait S-Frame - Standard

RT-1889YSD	Aquaplast RT Variable Perf, Head-Only Portrait S-Frame, 3.2 mm, Standard
RT-1889KYSD	Fibreplast Variable Perf, Head-Only Portrait S-Frame, 3.2 mm, Standard



Variable Perf Head & Shoulder Portrait S-Frame

RT-1892YSD	Aquaplast RT Variable Perf, Head & Shoulder Portrait S-Frame, 3.2 mm
RT-1892KYSD	Fibreplast Variable Perf, Head & Shoulder Portrait S-Frame, 3.2 mm